


**DUO-LOCK HAIMER MILL HPC, AlTiN, Ø f9 D1: 16mm**

**Order data**

Order number	220323 16
GTIN	4034221125781
Item class	26Y

**Description**
**Version:**

**DUO-LOCK HAIMER MILL:** Can be used as a universal tool. Unique end face geometry for ramping and circular interpolation milling. First choice for applications with short overhangs.

**DUO-LOCK HAIMER MILL Power Series:** First choice for applications with long overhangs and unstable clamping conditions. For particularly smooth running on long overhangs it is preferable to use solid carbide extensions.

**Technical description**

Corner chamfer width at 45°	0.32 mm
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.08 mm
Overhang $L_1$	24 mm
DUO-LOCK interface	DL16
Tolerance nominal Ø	f8
recommended tightening torque	60 Nm
Corner chamfer angle	45 degrees
Width across flats AF	13 mm
Cutter Ø D	16 mm
Ø D <sub>2</sub>	15.5 mm

Overall length L	32 mm
Flute length L <sub>2</sub>	24 mm
Number of cutting edges Z	8
Coating	AlTiN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Spacing of the cutters	unequal spacing
Helix angle	35 degrees
Direction of infeed	horizontal
Cutting width a <sub>e</sub> for milling operation	0.05×D for side milling
Machining strategy	HPC
Through-coolant	no
suitable arbor	with threaded shank
Type of product	Cutter insert for milling

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	700 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	700 m/min	N
Alu > 10% Si	suitable only under restricted conditions	235 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	280 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	220 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	200 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	160 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	120 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	90 m/min	M

Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	S
GG(G)	suitable only under restricted conditions	200 m/min	K
Uni	suitable		
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		
dry	suitable		
Air	suitable		