



DUO-LOCK HAIMER MILL 90° HPC, Ø h6 D1: 16mm



Order data

Order number	220359 16
GTIN	4034221103215
Item class	26Y

Description

Version:

DUO-LOCK HAIMER MILL: Can be used as a universal tool. Unique end face geometry for ramping and circular interpolation milling. First choice for applications with short overhangs.

DUO-LOCK HAIMER MILL Power Series: First choice for applications with long overhangs and unstable clamping conditions. For particularly smooth running on long overhangs it is preferable to use solid carbide extensions.

Technical description

Tolerance nominal Ø	h6
Number of cutting edges Z	8
Ø D ₂	3.2 mm
DUO-LOCK interface	DL16
recommended tightening torque	60 mm
Width across flats AF	13 Nm
Overhang L ₁	6.4 mm
Chamfer mill	45 degrees
Feed f _z in steel < 900 N/mm ²	0.08 mm
Overall length L	20 mm

Cutter Ø D	16 mm
Coating	AlTiN
Tool material	Solid carbide
Countersink tip angle	90
Standard	Manufacturer's standard
Type	N
Direction of infeed	horizontal, oblique and vertical
Through-coolant	no
Machining strategy	HPC
Type of product	Threaded copy milling cutter

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	700 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	700 m/min	N
Alu > 10% Si	suitable only under restricted conditions	235 m/min	N
Steel < 500 N/mm ²	suitable	220 m/min	P
Steel < 750 N/mm ²	suitable	160 m/min	P
Steel < 900 N/mm ²	suitable	160 m/min	P
Steel < 1100 N/mm ²	suitable	120 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	80 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	60 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	35 m/min	S
GG(G)	suitable only under restricted conditions	130 m/min	K

Uni	suitable
Oil	suitable
wet maximum	suitable
wet minimum	suitable
dry	suitable
Air	suitable