

Garant
Slot drill HSS-Co8, uncoated, Ø e8 DC: 8,7mm


Order data

| | |
|--------------|---------------|
| Order number | 191000 8,7 |
| GTIN | 4045197098986 |
| Item class | 11W |

Description

Version:

Centre cutting edge geometry for plunging.

Application:

For milling **keyways** (slots) or pockets from the centre of the component.

Technical description

| | |
|---|----------------------------------|
| Cutting edge Ø D _c | 8.7 mm |
| Feed f _z for slot milling in steel < 750 N/mm ² | 0.02 mm |
| Number of effective teeth Z (peripheral side) | 2 |
| Shank Ø D _s | 10 mm |
| Flute length L _c | 11 mm |
| Overall length L | 61 mm |
| Coating | uncoated |
| Tool material | HSS Co 8 |
| Standard | DIN 327 D |
| Type | N |
| Tolerance nominal Ø | e8 |
| Helix angle | 30 degrees |
| Direction of infeed | horizontal, oblique and vertical |

| | |
|----------------------|------------------|
| Shank | DIN 1835 B to h6 |
| Through-coolant | no |
| Shank tolerance | h6 |
| Corner chamfer angle | 90 degrees |
| Colour ring | without |
| Type of product | Milling cutter |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 83 m/min | N |
| Alu > 10% Si | suitable only under restricted conditions | 37 m/min | N |
| Steel < 500 N/mm ² | suitable | 28 m/min | P |
| Steel < 750 N/mm ² | suitable | 23 m/min | P |
| Steel < 900 N/mm ² | suitable only under restricted conditions | 23 m/min | P |
| GG(G) | suitable only under restricted conditions | 23 m/min | K |
| CuZn | suitable only under restricted conditions | 55 m/min | N |
| Uni | suitable | | |
| wet maximum | suitable | | |