




Precision dial indicator shock-resistant, Measuring range / Body Ø: 10/58mm



Order data

Order number	432140 10/58
GTIN	7630041109900
Item class	45A

Description

Version:

Dimensions to DIN EN ISO 463, issue June 2006. **Shock-resistant** precision dial indicators. Clamping shank \varnothing 8 mm h6, hardened and ground. Outer ring of dial face can be rotated to zero the dial. Outer ring with 2 adjustable tolerance pointers. Central pointer for 1/100 mm reading, small pointer on sub-scale for 1 mm reading.

Optional extras:

Special contact points No. 434900; 434910; 434915.

Technical description

Clamping shank \varnothing h6	8 mm
Measuring range	0 - 10 mm
Calibration	C1
Gauging force	0.56 - 0.84 N
Reading per pointer revolution	1 mm
Graduation	0.01 mm

Scale divisions	1/100 mm
Body Ø	58 mm
Standard	DIN 878
Measurement variation MPE (measurement range)	15 µm
Rotatable dial face	yes
adjustable tolerance marks	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Services

DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5
Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	023000 10