



Cordless sheet metal shears, Type: M18BMS20-0



Order data

| | |
|--------------|-------------------|
| Order number | 078104 M18BMS20-0 |
| GTIN | 4002395006748 |
| Item class | 03L |

Description

Version:

Compact cordless sheet metal slitters / shears for clean, distortion-free cuts in steel up to max. 2.0 mm.

- **360° rotatable cutting head with 12 locking positions – ideal for accessing tight spaces.**
- **Electronic speed control.**
- **In-line design for the best possible control.**

Supplied with:

Without battery and without charger, in a cardboard box.

Note:

Suitable replacement batteries and chargers can be found under No. 073808 – No 073840.

Technical description

| | |
|--|----------------------|
| Battery voltage | 18 V |
| Radius of the smallest curve | 180 mm |
| Number of rechargeable batteries contained | 0 |
| Power supply | Mains operated |
| maximum vibration to EN | 1.5 m/s ² |
| Type of rechargeable battery | Lithium-ion |
| Weight | 2.3 kg |

| | |
|--|------------------------|
| Cutting width | 5 mm |
| suitable battery - supplier / battery type / voltage | Milwaukee type HB 18 V |
| suitable battery - supplier / battery type / voltage | Milwaukee type B 18 V |
| maximum cutting performance on aluminium | 3.2 mm |
| maximum cutting performance on steel | 2 mm |
| Type of product | Aviation snips |