

Garant**Cleaning propeller, Blade Ø: 160****Order data**

Order number	358950 160
GTIN	4062406792435
Item class	31E

Description**Version:**

- **Robust design.**
- **Opening and closing the vane by the speed of the spindle.**
- **Marked ends to the vanes, for optimum visibility.**
- **For installation in any toolholder with through-coolant capability.**

The machine must be started at 2000 rpm and slowly increased to 6000 rpm – 12000 rpm.

Advantage:

- **Efficient cleaning of clamping equipment, workpieces and work tables.**
- **Removal of accumulated chips and blowing out pockets of water.**
- **Perfect complement to the automated work process.**

Optional extras:

Spare cleaning propeller No. 358951 1K and 4K.

Technical description

Speed range	6000 - 12000 min ⁻¹
Shank Ø	20 mm

Type of product

Cleaning propeller

Accessories

Spare spring set 4 pcs 4

358953 4