



Angle grinder GWS, Type: 17125SINOX



Order data

Order number	077109 17125SINOX
GTIN	4059952576619
Item class	03C

Description

Version:

1700 W motor with speed-control electronics, ideal for instance for **grinding stainless steel**. Outstanding, ergonomic handle circumference: First-class ergonomics thanks to significantly reduced handle circumference.

High user protection & control: Kickback control, soft start, restart inhibit, overload protection, vibration damping and speed pre-selection.

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle.

Technical description

maximum disc Ø	125 mm
Packaging	cardboard
Special features	Kickback Control, restart inhibit
Power consumption	1700 W
AC supply voltage	230 V
Power supply	Mains-powered
Connection thread	M14
Restart block	yes

Soft start	yes
Manufacturer's designation	GWS 17-125 S INOX
Nominal voltage	230 V
Weight	2.4 kg
Mains frequency	50 Hz
Kick-back stop	yes
Speed range	1900 - 7800 min ⁻¹
Type of product	Angle grinder