



Carbide cutting disc, Disc Ø: 76mm



Order data

Order number	563423 76
GTIN	4059952567549
Item class	54B

Description

Version:

Thin cutting disc specially for restricted work spaces.
Steel disc with brazed-on carbide grit on the cutting edge.

Application:

For cutting wood, plastic, plasterboard.

Suitable for:

Cordless small angle grinder No. 077100.

Technical description

for material thicknesses	3 - 5 mm
Disc thickness	1.8 mm
maximum speed	20100 min ⁻¹
Disc Ø	76 mm
Bore Ø	10 mm
Reference body width	0.9 mm

Shape description	straight
recommended approach angle	Radius degrees
optimised for material	Plastic
optimised for material	Plasterboard
optimised for material	Wood
Propulsive equipment	Straight die grinder
Propulsive equipment	Angle grinder
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V_c	ISO code
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Uni	suitable		