



## Cordless hammer drill / driver, Type: M12FPD2-6



### Order data

Order number	070110 M12FPD2-6
GTIN	4058546029784
Item class	03L

### Description

#### Version:

- **Powerful cordless 2-speed hammer drill /screwdriver with multi-stage torque setting.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

FUEL™ compact cordless hammer drill/driver with only 152 mm tool length. 13-stage electronic torque adjustment plus drill step plus hammer drill mode.

#### Advantage:

Compact, rechargeable battery serves as a stand.

#### Supplied with:

Supplied with 2× Li-ion batteries, charger, carrying case (HD box) and belt clip.

#### Note:

See No. 073814 – 073816, 073827 and 073840 for suitable batteries and chargers.  
The suitable Bluetooth tracking module can be found under 070103 BTT-1.

## Technical description

Motor design	FUEL™
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
maximum twist drill size Ø in wood	35 mm
typical application	Strong
Battery capacity	6 Ah
maximum vibration to EN without hammer drill function	<2.5 m/s <sup>2</sup>
maximum torque	45 Nm
maximum twist drill size Ø in concrete	13 mm
Weight	1.5 kg
Manufacturer's designation	M12FPD-602X
maximum twist drill size Ø in steel	13 mm
Battery voltage	12 V
maximum speed 2nd speed	1550 min <sup>-1</sup>
Number of rechargeable batteries contained	2
Power supply	Rechargeable battery-powered
Packaging	Modular case (HD=Heavy Duty)
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 1st speed	0 - 450 min <sup>-1</sup>
maximum vibration to EN with hammer drill function	15.7 m/s <sup>2</sup>
Type of rechargeable battery	Lithium-ion
Suitable for material	Steel
Suitable for material	Masonry
Suitable for material	Masonry
Suitable for material	wood
Suitable for material	wood
Type of product	limpact drill /screwdriver

---

**Accessories**

Li-ion system M12B6 Battery type MB12	073829 MB12
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C