


**DUO-LOCK HAIMER MILL Power Series HPC, uncoated, Ø f9 D1/R: 10/2,0mm**

**Order data**

Order number	220307 10/2,0
GTIN	4034221141231
Item class	26Y

**Description**
**Note:**

DUO-LOCK HAIMER MILL PowerSeries: First choice for applications with long overhangs and unstable clamping conditions. For particularly smooth running on long overhangs it is preferable to use solid carbide extensions.

**Technical description**

Overall length L	20 mm
Feed $f_z$ for side milling in short-chipping aluminium	0.03 mm
Milling head Ø D	10 mm
Corner radius	2 mm
Width across flats AF	8 mm
Ø D <sub>2</sub>	9.6 mm
DUO-LOCK interface	DL10 mm
recommended tightening torque	20 Nm
Overhang L <sub>1</sub>	15 mm
Tolerance nominal Ø	f8
Number of cutting edges Z	4
Coating	uncoated

Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Spacing of the cutters	unequal spacing
Helix angle	37 degrees
Helix angle characteristic	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	0.5×D for side milling
Machining strategy	HPC
Through-coolant	no
Shank type	with threaded shank
Type of product	Cutter insert for milling

### User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable		
Alu > 10% Si	suitable only under restricted conditions		
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable only under restricted conditions		