

**DUO-LOCK extension, conical, steel, long Plain shank, DUO-LOCK interface / Ø DS: DL16/25****Order data**

Order number	220378 DL16/25
GTIN	4034221150165
Item class	26Y

Description**Version:**

Coated for optimum shrinking in and out.

Technical description

Recommended torque	60 Nm
Ø D ₂	15.5 mm
Shank Ø D _s	25 mm
DUO-LOCK interface	DL16
Overall length L	250 mm
Through-coolant	yes
Type of product	Threaded copy mill arbor