

**Stackable transport boxes with fixed sides, Usable depth × usable width:
800X500mm****Order data**

| | |
|--------------|----------------|
| Order number | 963560 800X500 |
| GTIN | 4251572701406 |
| Item class | 96l |

Description**Version:**

Sturdy stackable transport boxes made from sheet metal with W-post design and angled support. With sturdy folded wall section similar to pipes at the top, sturdy round beading in the wall and floor area as well as dimpled label field for freight stickers (freight stickers can be easily removed from the raised dimpled area). Sturdy stacking and attachment brackets with lifting eyes. Large containers can be lifted by crane using certified crane crossbar in vertical pull chains with hooks. Access height 100 mm.

Solid sides.

Colour:

Mouse grey RAL 7005.

Note:

Also available in the colours fire red RAL 3000, reseda green RAL 6011 and gentian blue RAL 5010. Please contact us.

Technical description

| | |
|---------------------------------------|--------|
| Stacking height maximum | 500 mm |
| Attachment brackets with lifting eyes | yes |
| Capacity | 400 mm |
| Width | 560 mm |

| | |
|--|--|
| Drive-in width | 360 mm |
| Stackable load | 5000 kg |
| Height | 570 mm |
| Weight | 27 kg |
| Colour | mouse grey RAL 7005 |
| Pass-under height | 100 mm |
| with fork insertion slots | no |
| Drive-in depth | 660 mm |
| mixed stacking of different sizes is possible. | no |
| Wall version | solid side |
| Stacking edge on 3 sides | no |
| Depth | 860 mm |
| can be lifted by crane | yes |
| Material | Sheet metal |
| stackable | yes |
| Safe working load | 1000 kg |
| Usable width | 500 mm |
| Usable depth | 800 mm |
| Type of product | Transport and stacking large container |