

**Pneum. random orbital sander CP7220CVE, Type: 7220CVE****Order data**

Order number	079654 7220CVE
GTIN	015451619435
Item class	03R

**Description****Version:**

The pneumatic orbital sander 079654 7220 CVE was developed specially for industrial grinding, surface preparation and pre-polishing applications and offers outstanding user comfort with its soft, palm-shaped handle.

No load speed: 12000 min<sup>-1</sup>

maximum air consumption: 486 l/min

Backing pad Ø: 150 mm

Stroke: 2.5 mm

Weight: 1.6 kg

Operating noise: 76 dB(A)

**Technical description**

Operating noise	76 dB(A)
Stroke	2.5 mm
Manufacturer's designation	CP7220 CVE
maximum air consumption	486 l/min

Weight	1.6 kg
maximum vibration to EN	1.4 m/s <sup>2</sup>
Backing pad Ø	150 mm
No load speed	12000 min <sup>-1</sup>
Type of product	Random orbital sanders