



Cordless linishing machine, Type: M18FBTS75



Order data

Order number	077331 M18FBTS75
GTIN	4058546374082
Item class	03L

Description

Version:

Powerful M18 cordless belt linisher with brushless POWERSTATE™ motor for quick material removal and reduced heat generation.

- **Equivalent alternating current power 900 watt.**
- **Running time up to 20 minutes with a 5.0 Ah battery.**
- **The tool-less adjustment knob permits optimum handling of the grinder for all applications.**
- **“Flush To Wall” allows the linishing machine to be used close to a vertical surface or in narrow corners.**
- **Can be used with dust bag or external extraction.**

Supplied with:

Without battery and without charger, including dust bag, in a box.

Note:

Suitable replacement batteries and chargers can be found under No. 073808 – No 073840.
Suitable linishing belts can be found under No. 558014.

Technical description

suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V

Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Linishing belt width	75 mm
Grinding area	90 × 135 mm
Power supply	Rechargeable battery-powered
Belt speed	230 - 410 m/min
Battery voltage	18 V
Weight without battery	3.9 kg
Linishing belt length	457
Type of product	Linishing machine