



## Cordless drill/driver without battery or charger, Type: M12FDD2-2



### Order data

Order number	070214 M12FDD2-2
GTIN	4058546376666
Item class	03L

### Description

#### Version:

#### MILWAUKEE – Cordless power drill / driver

Powerful cordless 2-speed drill / driver, reversible.

Sturdy **metal gearbox** for long working life.

**FIXTEC metal quick-clamping drill chuck** with spindle lock.

LED illumination of the working area. Handle with Softgrip coating for comfortable use.

- **Brushless POWERSTATE™ motor for more power and a compact shape (168 mm in length).**
- **REDLINK PLUS™ electronics for intelligent power management and overload protection.**
- **16-step electronic torque limit setting, plus drill steps.**

#### Advantage:

REDLINK PLUS™ electronics.

#### Note:

See from No. 073815 and No. 073840 for suitable replacement batteries and chargers.

### Technical description

Quick-clamping chuck range	1.5 - 13 mm
----------------------------	-------------

Power supply	Rechargeable battery-powered
maximum speed 1st speed	0 - 450 min <sup>-1</sup>
maximum twist drill size Ø in steel	13 mm
Motor design	Brushless motor
maximum torque hard	37 Nm
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
maximum twist drill size Ø in wood	35 mm
Weight	1.2 kg
maximum speed 2nd speed	1700 min <sup>-1</sup>
Packaging	cardboard
typical application	Strong
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Suitable for material	wood
Suitable for material	wood
Type of product	Drill/driver
USP1	12V, 2-speed
USP2	Brushless motor, quick-change chuck clamping range 1.5-13, without battery and charger

## Accessories

Offset screwdriving attachment Type WB1	073920 WB1
Offset screwdriving attachment Type OSD2	073920 OSD2
Battery charger Type M1218C	073840 M1218C
Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12
Battery charger Type M1218FC	073840 M1218FC