

Garant

Jobber drill with stepped tip HSS-E Stainless steel, uncoated, Ø DC h8: 5,5mm



Order data

| | |
|--------------|---------------|
| Order number | 114008 5,5 |
| GTIN | 4062406877095 |
| Item class | 11Q |

Description

Version:

Chamfers are nitrided. Particularly sturdy and robust due to the **strengthened core diameter**. Ground flutes, with high concentricity. Precision ground point. Three **drive flats on the shank** for use in a 3-jaw chuck.

- **Ideal for producing precise holes in sheet metal, pipes, and profiles.**
- **Reliable spot drilling without centring or centre punching – even on curved surfaces – thanks to innovative ground point.**
- **Oblique drilling possible without any problems after the first level of the drill tip has penetrated the material.**
- **Drilling with significantly less force required than with conventional DIN338 HSS drills – up to a diameter of 13 mm directly in the cordless drill/driver.**
- **Stable and secure form fit in the 3-jaw chuck.**
- **General use across a wide spectrum of materials including plastic, wood and acrylic without tearing or splintering.**
- **The drill does not rattle or dig in – even in the case of thin-walled materials.**
- **Burr-free drill exit.**
- **Ideal for drilling out bolts and rivets.**

With special cutter geometry also for use in stainless steels.

Recommendation:

Maximum drilling depth:

$$L_2 = L_C - 1.5 \times D_C$$

Technical description

| | |
|---|-------------|
| Feed f in steel < 750 N/mm ² | 0.1 mm/rev. |
| Standard | DIN 338 |

| | |
|--|-------------------------|
| Shank $\varnothing D_s$ | 5.5 mm |
| recommended maximum drilling depth L_2 | 48.8 mm |
| Tolerance nominal \varnothing | h8 |
| Number of cutting edges Z | 2 |
| Nominal $\varnothing D_c$ | 5.5 mm |
| Overall length L | 93 mm |
| Point angle | 118 degrees |
| Flute length L_c | 57 mm |
| Shank | Three drive flats shank |
| Coating | uncoated |
| Tool material | HSS E |
| Type | INOX |
| Through-coolant | no |
| Colour ring | blue |
| Type of product | Jobber drill |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|-------|----------|
| Alu plastics | suitable only under restricted conditions | | |
| Aluminium (short chipping) | suitable only under restricted conditions | | |
| Alu > 10% Si | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1100 N/mm ² | suitable only under restricted conditions | | |
| INOX < 900 N/mm ² | suitable | | |

| | | | |
|------------------------------|----------|----------|---|
| INOX > 900 N/mm ² | suitable | | |
| GG(G) | suitable | 30 m/min | K |
| CuZn | suitable | | |
| Oil | suitable | | |
| wet maximum | suitable | | |