

Garant
Solid carbide ball nose slot drill HPC, TiAlN, Ø f8 DC / D S: 12mm

Order data

Order number	207320 12
GTIN	4045197127792
Item class	11X

Description
Version:
Precision ground for very high accuracy requirements.

Tolerance: Radius contour = ± 0.005 mm.

Note:
Recommended successor product is No. 207246.
Technical description

No. of teeth Z	2
Cutting edge Ø D _c	12 mm
Feed f _z for side milling in steel < 1100 N/mm ²	0.073 mm
Feed f _z for copy milling in steel < 1100 N/mm ²	0.084 mm
Shank Ø D _s	12 mm
Overall length L	150 mm
Flute length L _c	16 mm
Helix angle	30 degrees
Radius R	6 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H

Tolerance nominal \varnothing	f8
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	0.03×D for copy milling
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	HPC
Colour ring	without
Type of product	Ball-nosed slot drill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	Suitable	200 m/min	P
Steel < 750 N/mm ²	Suitable	180 m/min	P
Steel < 900 N/mm ²	suitable	170 m/min	P
Steel < 1100 N/mm ²	suitable	130 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	125 m/min	P
INOX < 900 N/mm ²	suitable	70 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	60 m/min	M
GG(G)	suitable only under restricted conditions	280 m/min	K
CuZn	suitable only under restricted conditions	300 m/min	N
wet maximum	Suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	Suitable		

Services

Shank grinding Type HB

129100 HB