



## Carbide-tipped hammer drill SDS-max "8X", Ø×overall length: 16X340mm



### Order data

Order number	789206 16X340
GTIN	4059952532882
Item class	76K

### Description

#### Version:

New generation **EXPERT SDS-max "8X"** with welded 4-edge solid carbide head. Shaped cutters for high drilling performance, long working life and low wear. No digging in when drilling in reinforced concrete.

#### Special carbide insert geometry for longer tool lives.

Drill head with square cross section from Ø 16 mm.

#### Application:

For drilling concrete, natural stone, and masonry.

#### Note:

Generation SDS-max-7 drill (with embedded carbide cutting edges, soldered) in the size 35×520 – 52×520 under No. 789204.

### Technical description

Ø	16 mm
overall length	340 mm
Flute length	200 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Max
Type of product	Masonry drill

