

## Garant

### Solid carbide HPC drill, plain shank DIN 6535 HA, TiAlSiN, Ø DC m7: 16,01-Xmm



## Order data

Order number	122480 16,01-X
GTIN	4067263000723
Item class	11E

## Description

### Version:

Specially for machining **titanium-based and nickel-based alloys**. With wear-resistant, ultra-smooth TiAlSiN high-performance coating for a **long tool life** combined with **optimum bore quality** and **very low burr formation**.

### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

HB and HE shanks are available at the same price as HA.

For **HB**: use order **No. 122481**.

For **HE**: use order **No. 122480** and **129100HE**. Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by +/-10% (minimum 1 piece).

Minimum order quantity: 3 pcs

Delivery time: 7 working weeks

## Technical description

Overall length L	123 mm
Shank Ø D <sub>s</sub>	18 mm
Tolerance nominal Ø	m7
Flute length L <sub>c</sub>	73 mm
Number of cutting edges Z	2
recommended maximum drilling depth L <sub>2</sub>	46 mm

Ø range	16.01 - 18 mm
Standard	DIN 6537
Coating	TiAlSiN
Tool material	Solid carbide
Version	4×D
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	pink
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Ti > 850 N/mm <sup>2</sup>	suitable		
Inconel	suitable		
wet maximum	suitable		