



Metal chop saw, Type: 72365460



Order data

Order number	078244 72365460
GTIN	4014586894447
Item class	03F

Description

Version:

Semi-stationary chop saw for efficient and quick cutting of components both in the workshop and on the construction site.

- **Greatest possible work progress thanks to a high-torque motor with low speeds**
- **Precise results and little reworking thanks to minimal discolouration and low burr formation due to cold cutting**
- **High surface quality due to special saw blades for different metals**
- **Up to 100% spark free and no dust formation due to cold cutting**
- **Well-balanced grip design for better guidance**
- **High-precision, durable steel construction**
- **Base of cast aluminium**
- **Soft starting ensures a slow start-up of the motor, which protects the mechanism**
- **Quick-release device for table clamp**
- **Convenient chamfer and angle adjustment from 0° to 45°**
- **Depth stop+simple saw blade change**

Application:

- **Sawing of steel and metal profiles.**
- **Production of separating and mitre cuts.**
- **Machining of pipes, metal bolts, angle irons, bar material.**

Supplied with:

1 pc. chop saw, 1 pc. saw blade for structural steel, 1 pc. combination wrench: Hex socket, 6 mm and Phillips head PH 2, 1 pc. hex socket 8 mm.

Technical description

Soft start	yes
Weight	24.4 kg
Manufacturer's designation	MKAS 355
AC supply voltage	230 V
maximum cutting depth 90°	120 mm
Nominal voltage	230 V
Power supply	Mains-powered
Saw blade Ø	355 mm
maximum cutting depth 45°	90 mm
maximum speed	1300 min ⁻¹
Mains frequency	50 Hz
Power consumption	1800 W
Type of product	Saw