



**HOLEX CleverDrill HSS jobber drill N, uncoated, Ø DC h8: 14mm**

**Order data**

Order number	GG4031 14
GTIN	4067263102014
Item class	GGN

**Description**
**Version:**

**HOLEX CleverDrill:** Sturdy drill for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

**Same as No. 114031.**

**Recommendation:**
**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c$$

**Note:**

**Successor product to No. 114030.**

Size 13.5 – 16: With stepped shank Ø 12.7 mm.

**Technical description**

Shank	Plain shank
Nominal Ø D <sub>c</sub>	14 mm
Point angle	118 degrees
Tolerance nominal Ø	h8
Shank Ø D <sub>s</sub>	12.7 mm
recommended maximum drilling depth L <sub>2</sub>	87 mm

Number of cutting edges Z	2
Overall length L	160 mm
Standard	DIN 338
Flute length $L_c$	108 mm
Feed f in steel < 750 N/mm <sup>2</sup>	0.16 mm/rev.
Contents	20
Series	CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	80 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	60 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	35 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	32 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	22 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	18 m/min	P
GG(G)	suitable only under restricted conditions	30 m/min	K
CuZn	suitable	40 m/min	N

Oil	suitable
wet maximum	suitable

---

## Accessories

HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 14	114031 14
----------------------------------------------------------------	-----------