


HOLEX CleverDrill HSS jobber drill N, uncoated, Ø DC h8: 12,5mm

Order data

Order number	GG4031 12,5
GTIN	4067263101987
Item class	GGN

Description
Version:

HOLEX CleverDrill: Sturdy drill for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Same as No. 114031.

Recommendation:
Maximum drilling depth:

$$L_2 = L_C - 1.5 \times D_C$$

Note:

Successor product to No. 114030.

Size 13.5 – 16: With stepped shank Ø 12.7 mm.

Technical description

Standard	DIN 338
Shank	Plain shank
Shank Ø D _s	12.5 mm
Nominal Ø D _c	12.5 mm
recommended maximum drilling depth L ₂	82.3 mm
Tolerance nominal Ø	h8

Point angle	118 degrees
Flute length L_c	101 mm
Feed f in steel $< 750 \text{ N/mm}^2$	0.16 mm/rev.
Overall length L	151 mm
Number of cutting edges Z	2
Contents	20
Series	CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	80 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	60 m/min	N
Alu $> 10\% \text{ Si}$	suitable only under restricted conditions	50 m/min	N
Steel $< 500 \text{ N/mm}^2$	suitable	35 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	32 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	22 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable only under restricted conditions	18 m/min	P
GG(G)	suitable only under restricted conditions	30 m/min	K
CuZn	suitable	40 m/min	N

Oil	suitable
wet maximum	suitable

Accessories

HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 12,5	114031 12,5
HOLEX CleverDrill jobber drill set HSS No. 114031 in a case Type 1-13	115051 1-13
HOLEX CleverDrill HSS jobber drill set No. 114031 as a refill set Type 1-13	115056 1-13