



## Oscillating saw and mitre saw BITURBO Cordless, Type: GCM18216DC



### Order data

Order number	078232 GCM18216DC
GTIN	4059952608402
Item class	03B

### Description

#### Version:

Cordless pivoting saw and mitre saw.

- **Excellent cutting capacity with a large cutting depth of 70 mm.**
- **Best mobility thanks to its low weight and outstanding ergonomics.**
- **User interface for speed pre-selection.**
- **Tool-free saw blade change.**

#### Supplied with:

Saw blade Ø 216 mm, hold-down clamp, SDS nut, GCY 42 Bluetooth module.

### Technical description

maximum mitre angle left	52 degrees
electronic speed pre-selection	yes
maximum inclination angle right	47 degrees
maximum inclination angle left	47 degrees
Saw blade Ø	216 mm
maximum cutting depth 45°	45 mm
Power supply	Mains operated

maximum mitre angle right	60 degrees
Battery voltage	18 V
maximum speed	4500 min <sup>-1</sup>
Saw blade bore Ø	30 mm
Type of rechargeable battery	Lithium-ion
suitable battery - supplier / battery type / voltage	Bosch 18 V
Weight	15.3 kg
maximum cutting length 90°	300 mm
Nominal voltage	18 V
Number of rechargeable batteries contained	0
Manufacturer's designation	GCM 18V-216 DC
maximum cutting depth 90°	70 mm
Packaging	cardboard
Type of product	Saw