


HAIMER MILL end mill, AlTiN, Ø f9 DC: 12mm

Order data

Order number	220293 12
GTIN	2050002068339
Item class	26X

Description
Version:

For **general-purpose use** in steel materials and high-alloy steels, especially stainless steel. With **cylindrical core** for optimised tool stiffness when milling slots. Reliable processes guaranteed when ramping and during circular interpolation milling thanks to **special end face geometry**.

Note:

For **HB** use order **No. 220293**.

Tool holders with the SAFE-LOCK pull-out protection can be found under clamping technology.

Technical description

Feed f_z for slot milling in steel < 900 N/mm ²	0.066 mm
Direction of infeed	horizontal, oblique and vertical
Helix angle	38 degrees
Corner chamfer angle	45 degrees
Shank	DIN 6535 HB to h6
Overall length L	95 mm
Recess Ø D ₁	11.4 mm
Tolerance nominal Ø	f8
Corner chamfer width at 45°	0.24 mm
Flute length L _c	36 mm
No. of teeth Z	4

Feed f_z for side milling in steel $< 900 \text{ N/mm}^2$	0.078 mm
Overhang length L_1 incl. recess	48 mm
Cutting edge $\varnothing D_c$	12 mm
Shank $\varnothing D_s$	12 mm
Coating	AlTiN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	$0.05 \times D$ for side milling
Cutting width a_e for milling operation	$0.05 \times D$ for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions		
Alu $> 10\% \text{ Si}$	suitable only under restricted conditions		
Steel $< 500 \text{ N/mm}^2$	suitable		
Steel $< 750 \text{ N/mm}^2$	suitable		
Steel $< 900 \text{ N/mm}^2$	suitable		
Steel $< 1100 \text{ N/mm}^2$	suitable		
INOX $< 900 \text{ N/mm}^2$	suitable		

INOX > 900 N/mm ²	suitable
Ti > 850 N/mm ²	suitable only under restricted conditions
GG(G)	suitable only under restricted conditions
Uni	suitable
Oil	suitable
wet maximum	suitable
wet minimum	suitable
dry	suitable
Air	suitable