




## Solid carbide milling cutter, TiAlN, Ø h10 DC: 8mm



### Order data

Order number	202760 8
GTIN	4045197118042
Item class	12X

### Description

#### Version:

Eccentric relief ground.

**Without** 45° cutting edge chamfer.

### Technical description

No. of teeth Z	4
Cutting edge Ø D <sub>c</sub>	8 mm
Feed f <sub>z</sub> for side milling in steel < 900 N/mm <sup>2</sup>	0.045 mm
Shank form	HB
Feed f <sub>z</sub> for slot milling in steel < 900 N/mm <sup>2</sup>	0.04 mm
Shank Ø D <sub>s</sub>	8 mm
Overall length L	70 mm
Flute length L <sub>c</sub>	22 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	h10
Helix angle	30 degrees
Corner chamfer angle	90 degrees
Coating	TiAlN

## Data sheet

Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Cutting width $a_e$ for milling operation	0.3×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Steel < 900 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	35 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	80 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	Suitable		
wet minimum	Suitable only under restricted conditions		
dry	Suitable only under restricted conditions		
Air	Suitable only under restricted conditions		

**Suitable products**

<https://www.hoffmann-group.com/GB/en/hom/p/202760-8>

---