

**HOLEX**

**Indexable face mill 45°, with bore, Ø D / number of effective cutting edges Z:  
63/5mm**



## Order data

Order number	214202 63/5
GTIN	4067263001904
Item class	220

## Description

**Version:**

Without through-coolant feed.

**Note:**

Use GARANT torque screwdriver TQ No. **211750 size 5.7** with bit No. **674252 size 20IP**.

## Technical description

Mounting bore Ø	22 mm
Number of cutting edges Z	5
suitable indexable insert	SE.. 1204..
Cutting edge Ø D <sub>c</sub>	63 mm
Overall length L <sub>tot</sub>	48 mm
maximum external Ø D <sub>max</sub>	76 mm
Pack of insert screws	219848 (20IP; 5.7 Nm)

Shank type	with bore
Setting angle $\kappa$	45 degrees
Spacing of the cutters	unequal spacing
Machining strategy	MTC
Standard	Works standard
Type of product	Face Mill

---

## Accessories

Set of insert screws 10 pieces	219848
--------------------------------	--------