

Garant GRIDLINE

eLevel workstation with bamboo worktop, Length: 2000/2mm



Order data

Order number	920016 2000/2
GTIN	4067263001430
Item class	91P

Description

Version:

Workstation eLevel height steplessly adjustable electrically. Height adjustment by an electronic control panel. Control panel with display and memory functions. Push-button adjustment for a suitable **height of the entire workstation**.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift column anodised aluminium, **not configurable**.

Side and rear wall RAL 7035 light grey **powder-coated, configurable**.

Note:

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 920350 (crush hazard).**

Sizes with .../2 are fitted with an alternative lift unit. Technical data is similar to the previous lift units, slight deviations. Control panel is visually different for these sizes, but functionally the same.

- **Entry of these article numbers only after prior consultation with Technical Purchasing P93, Tel. +49 89 8391 9165, current availability must be checked.**
- **Observe the maximum load capacity, under no circumstances must it be exceeded! Particularly important in the planning of support column structures.**

Technical description

Worktop length	2000 mm
Worktop depth	800 mm
Model	eLevel
Plug type, input	F
Height adjustment range (worktop surface) from – to	670 - 990 mm
Nominal voltage	250 V
Material of worktop	Bamboo
Control panel with display and memory functions	yes
Principle of height adjustment	complete structure
Width	2000 mm
Stepless height adjustment	yes
Depth	800 mm
Series	Workstation
Worktop thickness	50 mm
Weight	93 kg
Height adjustment workstation	670-990 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	electrical
Insert thickness	50 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table