


Garant**Electronic torque analyser, maximum torque: 1000N·m****Order data**

Order number	654413 1000
GTIN	4067263152453
Item class	61D

Description**Version:**

For use of mechanical and digital branded torque wrenches (not HCT) and screwdrivers, and setting and checking triggering, indicating, right-hand and left-hand turning torque wrenches and screwdrivers.

- **Display:** Large sharp contrast illuminated 2.8 inch TFT display with double scale with viewing angle stability. With memory capacity display.
- **Memory capacity:** 1000 measurement values with time stamp (incl. date and time) and 20 configurable test cases.
- **Modes:** Tracking display (Track), trigger point sensing (First-Peak) and peak value display (Peak Hold).
- **Attachment:** can be attached to flat surfaces (table, wall, etc.) using 4 screws (M10).
- **3 recesses** for secure storage of adapters (increaser piece).
- **Data output:** Available via USB-C. The data can be exported as a .csv file.
- **Password protection:** available as protection against unauthorised access to the menu (master password) and for verifying test cases. In addition, you can set that reworking a test case that has been performed incorrectly requires input of a password.
- **Warning signals:** visual (change of colour on the display) and acoustic (buzzer). The pre-warning point can be configured individually. The acoustic warning signal can be disabled if desired.
- **Protection class IP40**

- **Languages: German, English, Spanish, Italian, French.**
- **Factory settings: Can be reset to the factory settings.**
- **Displays the software version with the serial number and date of the last calibration. The date of the next calibration can be set on the torque analyser.**

Units of measurement: Nm, lbfft, lbfin.

Function:

IP40: Protected against penetration by foreign bodies with $\varnothing > 1$ mm. However, tools and wires should be kept away and there is no protection against water.

Accuracy:

Clockwise and anti-clockwise: +/- 1%.

Supplied with:

USB-C data cable (1.8 m), power supply unit, country adapter (types A, C, G and I), certificate of conformity. Supplied in a sturdy plastic case.

Note:

Suitable additional adapters can be found under No. 649550 and No. 650006.

Technical description

maximum torque	1000 Nm
Display unit width	171 mm
Power supply	Mains operated
Resolution	1 Nm
Torque measuring accuracy	± 1 %
External hexagon drive	27 mm
Display unit depth	161 mm
Measuring range	100 - 1000 Nm
Weight	3.3 kg
IP Index of Protection	IP 40
Display unit height	86 mm
Direction of tightening	For right and left-hand tightening
Interface	USB interface
Test certificate	Manufacturer's test certificate
Calibration	O4
Type of product	Torque analyser

Services

Calibration clockwise / anti-clockwise Torque analyser /
sensor maximum torque 1000/2 N·m

020140 1000/2

DAkkS calibration clockwise / anti-clockwise Torque
analyser / sensor maximum torque 1000/2 N·m

020150 1000/2