



HOLEX Clever Tap machine tap, uncoated, UNC: 10-24



Order data

Order number	133353 10-24
GTIN	4067263161837
Item class	12H

Description

Version:

With spiral point.

HOLEX Clever Tap:

Sturdy tap for conventional standard applications. High-quality HSS-E tool material and geometry for steels. Surface: Bronze-coloured tempered thread profile.

Application:

For UNC uniform coarse threads ASME – B1.1.

Thread type: UNC

Tool material: HSS E

Standard: DIN 371

Threads per inch: 24

Thread Ø: 4.83 mm

Overall length L: 70 mm

Shank Ø D_s: 6 mm

Shank square □: 4.9 mm

Tapping hole Ø: 3.9 mm

Technical description

Thread Ø	4.83 mm
Tapping hole Ø	3.9 mm
Threads per inch	24
Thread pitch	1.058 mm
Thread size	10-24 UNC
Tool material	HSS E

Overall length L	70 mm
Shank $\varnothing D_s$	6 mm
Thread depth	14.49 mm
Number of cutting edges Z	3
Number of clamping slots	3
Shank square \square	4.9 mm
Standard	DIN 371
Thread type	UNC
Coating	uncoated
Flank angle	60°
Tolerance class	2B
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Taps

User data

	Suitability	V_c	ISO code
Aluminium	suitable only under restricted conditions	13 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	12 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P

Steel < 900 N/mm ²	suitable only under restricted conditions	6 m/min	P
Oil	suitable		
wet maximum	suitable		