



HOLEX Clever Tap machine tap, uncoated, UNC: 3/4-10



Order data

Order number	133353 3/4-10
GTIN	4067263161905
Item class	12H

Description

Version:

With spiral point.

HOLEX Clever Tap:

Sturdy tap for conventional standard applications. High-quality HSS-E tool material and geometry for steels. Surface: Bronze-coloured tempered thread profile.

Application:

For UNC uniform coarse threads ASME – B1.1.

Thread type: UNC

Tool material: HSS E

Standard: DIN 376

Threads per inch: 10

Thread Ø: 19.05 mm

Overall length L: 125 mm

Shank Ø D_s: 14 mm

Shank square □: 11 mm

Tapping hole Ø: 16.5 mm

Technical description

Number of clamping slots	3
Thread depth	57.15 mm
Threads per inch	10
Thread pitch	2.54 mm
Shank Ø D _s	14 mm

Thread Ø	19.05 mm
Standard	DIN 376
Tool material	HSS E
Shank square □	11 mm
Number of cutting edges Z	3
Thread size	3/4-10 UNC
Thread type	UNC
Tapping hole Ø	16.5 mm
Overall length L	125 mm
Coating	uncoated
Flank angle	60 °
Tolerance class	2B
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Taps

User data

	Suitability	V _c	ISO code
Aluminium	suitable only under restricted conditions	13 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	12 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P

Steel < 900 N/mm ²	suitable only under restricted conditions	6 m/min	P
Oil	suitable		
wet maximum	suitable		