

Garant
GARANT Diabolo solid carbide ball nose slot drill HPC, TiAlN, Ø f8 DC: 5mm

Order data

Order number	207372 5
GTIN	4045197600387
Item class	11X

Description
Version:
GARANT Diabolo:

Special geometry, coating and carbide for hard machining.

Taper transition with 1.5° (angle α).

Tolerance: Radius contour = ± 0.005 mm.

Technical description

Overhang length L_1 incl. recess	20 mm
Cutting edge $\varnothing D_c$	5 mm
L_2	40 mm
Feed f_z for copy milling in steel < 65 HRC	0.048 mm
Recess $\varnothing D_1$	4.8 mm
$\varnothing D_2$	5.9 mm
No. of teeth Z	2
Shank $\varnothing D_s$	6 mm
Overall length L	80 mm
Flute length L_c	6 mm
Helix angle	30 degrees
Radius R	2.5 mm
Series	Diabolo

Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	f8
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	$0.05 \times D$ for copy milling
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	HPC
Colour ring	red
Type of product	Ball-nosed slot drill

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable	180 m/min	P
Steel < 50 HRC	suitable	170 m/min	H
Steel < 55 HRC	suitable	150 m/min	H
Steel < 60 HRC	suitable	135 m/min	H
Steel < 65 HRC	suitable	95 m/min	H
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------

