



Solid carbide milling cutter, TiAlN, Ø h10 DC: 3mm

Order data

Order number	202760 3
GTIN	4045197118004
Item class	12X

Description
Version:

Eccentric relief ground.

Without 45° cutting edge chamfer.

Technical description

Feed f_z for slot milling in steel < 900 N/mm ²	0.01 mm
Shank form	HA
Cutting edge Ø D_c	3 mm
Feed f_z for side milling in steel < 900 N/mm ²	0.011 mm
No. of teeth Z	4
Shank Ø D_s	3 mm
Overall length L	38 mm
Flute length L_c	12 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA to h6
Tolerance nominal Ø	h10
Helix angle	30 degrees
Corner chamfer angle	90 degrees
Coating	TiAlN

Data sheet

Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable	60 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	35 m/min	H
INOX < 900 N/mm ²	suitable	80 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	60 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	Suitable		
wet minimum	Suitable only under restricted conditions		
dry	Suitable only under restricted conditions		
Air	Suitable only under restricted conditions		

