

Garant
Chamfer mill 45°, Weldon shank, Ø D: 8mm

Order data

Order number	216100 8
GTIN	4045197133458
Item class	210

Description
Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.

Technical description

Overall length L_{tot}	80 mm
Pack of insert screws	219804 (15IP; 3.8 Nm)
Overhang L_1	17 mm
suitable indexable insert	SD.. 090308
maximum chamfering $\varnothing D_{max}$	20.2 mm
Shank $\varnothing D_s$ h6	16 mm
Number of cutting edges Z	1
$\varnothing D$	8 mm
Shank type	Weldon shank
Chamfering angle reverse	45 degrees
Setting angle κ	45 degrees
Through-coolant	yes
Tool exchange	PowerCard
Type of product	Indexable end mill

Accessories

Set of insert screws10-piece	219804
Torque screwdriver, fixed setting set torque 3,8 N·m	211750 3,8
Set of insert screws10-piece	219805
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
