

Garant
Chamfer mill 45°, with thread, Ø D: 16mm

Order data

Order number	216102 16
GTIN	4045197469915
Item class	210

Description
Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.

Technical description

Overall length L_{tot}	28 mm
Cutting edge $\varnothing D_c$	16 mm
maximum chamfering $\varnothing D_{max}$	28.3 mm
Mounting thread M	M10
suitable indexable insert	SD.. 090308
$\varnothing D_2$	17.7 mm
Pack of insert screws	219805 (15IP; 3.8 Nm)
Overhang L_1	18 mm
Minimum infeed $\varnothing D_{min}$	28.5 mm
$\varnothing D_1 h_6$	10.5 mm
Number of cutting edges Z	2

Shank type	with thread
Chamfering angle reverse	45 degrees
Through-coolant	yes
Tool exchange	PowerCard
Type of product	Indexable end mill

Accessories

Torque screwdriver, fixed setting set torque 3,8 N·m	211750 3,8
Set of insert screws10-piece	219805
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Set of insert screws10-piece	219804