



## Pipework linisher, Type: 72227560



### Order data

Order number	077715 72227560
GTIN	4014586895864
Item class	03F

### Description

#### Version:

Pipework linisher with **extremely high stock removal rate**. Ideal for **working on pipes and pipe elbows**, cleaning up, removal of colouration, grinding weld seams, preparation for polishing, and polishing to mirror finish. Speed range variable for grinding, linishing, and polishing belts. **Improved belt guidance**. Tube grinder for narrow radii, continuously adjustable speed for grinding, satin finishing and high-gloss polishing.

Minimum wall distance 50 mm.

#### Advantage:

- **Effective removal of weld seams through optimum cutting speed of the sanding belts.**
- **Continuously adjustable speed for grinding, satin finishing and high-gloss polishing of already assembled handrails.**
- **Flexible sanding belts adapt optimally even to narrow pipe bends and thus result in seamless surfaces.**
- **360° peripheral grinding in just 2 steps.**
- **Optional deflection rollers for a small distance from the wall.**
- **Safeguard against accidental restart.**
- **Dust-protected ball bearings.**

#### Supplied with:

Pipework grinder FEIN RS 17-70 E.

Supplied without accessories in a box.

#### Note:

Linishing belts can be found from No. 558011.

## Technical description

Speed range	2700 - 8500 min <sup>-1</sup>
Soft start	yes
pipework Ø for linishing	8 - 80 mm
Power consumption	1700 W
Power supply	Mains-powered
Nominal voltage	230 V
Restart block	yes
Cable length	4 m
Tape width	20; 40 mm
maximum belt speed	9 - 27 mm/s
Weight	4.64 kg
Manufacturer's designation	RS 17-70 E
Band length	815 mm
Type of product	Pipework linishers