



HOLEX Clever Tap machine tap, uncoated, UNF: 10-32



Order data

Order number	138004 10-32
GTIN	4067263161462
Item class	12H

Description

Version:

HOLEX Clever Tap:

Sturdy tap for conventional standard applications. High-quality HSS-E tool material and geometry for steels. Surface: Bronze-coloured tempered thread profile. **HSS-E**

Application:

For UNF uniform fine threads ASME – B1.1.

Technical description

Number of cutting edges Z	3
Tool material	HSS E
Thread pitch	0.794 mm
Shank square □	4.9 mm
Tapping hole Ø	4.1 mm
Shank Ø D _s	6 mm
Overall length L	70 mm
Thread size	10-32 UNF
Thread type	UNF
Standard	DIN 371
Thread Ø	4.83 mm
Threads per inch	32

Number of clamping slots	3
Thread depth	12 mm
Series	CleverTap
Coating	uncoated
Flank angle	60 degrees
Tolerance class	2B
Taper lead form	C
Helix angle	40 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Taps

User data

	Suitability	V _c	ISO code
Aluminium	suitable only under restricted conditions	13 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	12 m/min	P
Steel < 750 N/mm ²	suitable	12 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	6 m/min	P
Oil	suitable		
wet maximum	suitable		

