

**HOLEX Clever Tap machine tap, uncoated, UNF: 9/16-18****Order data**

Order number	133404 9/16-18
GTIN	4067263161967
Item class	12H

Description**Version:****With spiral point.****HOLEX Clever Tap:**

Sturdy tap for conventional standard applications. High-quality HSS-E tool material and geometry for steels. Surface: Bronze-coloured tempered thread profile.

Application:

For UNF uniform fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E

Standard: DIN 374

Threads per inch: 18

Thread Ø: 14.29 mm

Overall length L: 100 mm

Shank Ø D_s: 11 mm

Shank square □: 9 mm

Tapping hole Ø: 12.9 mm

Technical description

Thread type	UNF
Shank square □	9 mm
Thread size	9/16-18 UNF
Tool material	HSS E
Tapping hole Ø	12.9 mm

Threads per inch	18
Standard	DIN 374
Overall length L	100 mm
Number of clamping slots	3
Number of cutting edges Z	3
Thread depth	57.16 mm
Thread \varnothing	14.29 mm
Shank $\varnothing D_s$	11 mm
Thread pitch	1.411 mm
Coating	uncoated
Flank angle	60 °
Tolerance class	2B
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Taps

User data

	Suitability	V_c	ISO code
Aluminium	suitable only under restricted conditions	13 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	12 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P

Steel < 900 N/mm ²	suitable only under restricted conditions	6 m/min	P
Oil	suitable		
wet maximum	suitable		