

# Yale

**UNO plus A lever hoist with round steel link chain, Safe working load: 0,75t**



## Order data

Order number	086017 0,75
GTIN	4053981776965
Item class	08Y

## Description

### Version:

Robust construction made of sheet steel in compact design. Smooth-running **chain release**. Chain guides for trouble-free chain running.

### Application:

Standard, handy all-purpose hoist for versatile applications.

### Note:

The principle of the **threaded load pressure brake** is that the axial braking force is generated by the load itself and is thus proportional to the weight of the load. The load is safely held in all positions; to lower it, the difference between the braking torque and load torque must be overcome. All Yale all-purpose hoists are equipped with this device.

The automatic **chain release** permits **quick run-out** of the unloaded chain; when the load is applied, the **threaded load pressure brake** automatically takes effect again and the load is safely held.

The **slip clutch** (optional feature) prevents unduly high loading, and thus increases the working life of the lifting gear.

**ATEX version on request**

## Technical description

Chain release.	yes
Safe working load	750 kg
Lifting force at nominal load	22 daN
Housing material	Sheet steel
Number of chains	1
Standard lifting height	1.5 m
Safe working load in t	0.75 t
Weight	6.3 kg
Type of product	Lever hoist / chain pull