


X.LT...ER-D41, X500, Indexable insert size: 16mm

Order data

Order number	221938 16
GTIN	4059782506190
Item class	28F

Description
Version:

Particularly thick indexable inserts with ground wiper chamfer.

Note:

Standard application values for $a_e = 0.3 \times D$.

Technical description

Indexable insert size	16
Type	UNI
ISO code indexable insert	XELT160512-ER-D41
Programming radius at $a_{p \max}$	4.18 mm
Corner radius	1.2 mm
Grade	X500
Tool material	Carbide
Feed f_z per tooth	0.15 - 1 mm
Number of changes/inserts	4

Type of product

Indexable insert for milling

User data

	Suitability	V_c	ISO code
Steel < 750 N/mm ²	suitable	230 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	140 m/min	P
INOX < 900 N/mm ²	suitable	200 m/min	M
INOX > 900 N/mm ²	suitable	170 m/min	M
Ti > 850 N/mm ²	suitable	60 m/min	S
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		