



Tap bit, vaporised, M: M8



Order data

Order number	130992 M8
GTIN	4067263295860
Item class	12H

Description

Version:

With 1/4 inch hexagon shank to DIN 3126 C 6.3.

Application:

Ideal for repair and assembly work in mobile situations.

Technical description

Taper lead form	B
Tapping hole \varnothing	6.8 mm
Overall length L	40 mm
Standard	Works standard
Thread pitch	1.25 mm
Recess $\varnothing D_1$	6 mm
Type of threading tool	Serial hand taps
Thread standard	DIN 13
Flute length L_c	18 mm
Cutting direction	right-hand
Coating	vaporised
Thread type	M
Tool material	HSS

Tolerance class	ISO 2 6H
Flank angle	60 degrees
Application for type of drilling	up to 1.5×D for through holes
Type of product	Tap bit

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable only under restricted conditions		
INOX < 900 N/mm ²	suitable only under restricted conditions		
Oil	suitable		