

**Garant**
**Surface roughness measuring instrument without printer, Type: ST2**

**Order data**

Order number	499021 ST2
GTIN	4067263410706
Item class	41M

**Description**
**Version:**

Portable roughness measuring instrument for precise roughness measurement and documentation conforming to standards, using the stylus tracing method. **With integral (removable) calibration standard.** Large illuminated 4.3 inch TFT touch display. Display can be rotated. Feed unit can be operated as part of the main unit and separately. LED light bar for status display (green - battery status display, red - error message, blue - measurement, data transmission), integral height adjustment, data saving as TXT, X3P, CSV and PDF files. Gauss filter to ISO 16610 – 21 (supersedes DIN EN ISO 11562), special filter to DIN EN ISO 13565 – 1, IS filter to DIN EN ISO 3274 (can be switched off). **Tolerance monitoring:** It can be quickly determined whether the measured value is within the specified tolerance from the colour of the characteristic values (green – inside and red – outside the tolerance). IATF 16949 compliant – reliable traceability.

**Advantage:**

- **Switch on and start measuring immediately – intuitively without training, e.g. automatic cutoff selection, information on roughness characteristics directly on the device, pre-set measuring programs and quick access to desired functions by saving favourites in the display.**
- **Transmission of the measuring results via Bluetooth or alternatively by a cable connection. Compatible with the optional HCT (Hoffmann Group Connected Tools)**

**mobile app. Available free of charge for Android and iOS. Can also be used via a Human Interface Device (HID).**

- **Summarise multiple measurements (for example, for a series) in a PDF log using the HCT mobile app. Adding a photo (for example, component or measurement setup and making individual comments on the log possible.)**
- **Documentation by optional thermal printer for printing out the profile or the results via Bluetooth or cable connection.**
- **The software interface of the device can be switched between bright and dark views depending on the lighting conditions.**
- **Ergonomic stand ensures optimum viewing angle.**

#### **Supplied with:**

Supplied with feed unit, manual Vee, stand No. 499023, standard probe No. 499004 size 6 – 350, integral roughness standard incl. factory calibration certificate No. 499575, integral height adjustment, probe guard, charger / mains adapter, instruction manual, mini-USB cable, USB Bluetooth dongle No. 499024, extension cable, feed unit, carrying case.

#### **Optional extras:**

Spare / special probe No. 499004.

Probe extension No. 499008.

Probe guard No. 499038.

Stand No. 499011; 498857.

Data cable for MarConnect No. 498941 size USB2.

#### **Spare part:**

Battery No. 499548 size AKKU.

## **Technical description**

Evaluation unit length	160 mm
Power supply	Rechargeable battery-powered
Roughness standards	DIN / ISO / JIS / ASME
maximum measuring range	0.014 in
Evaluation unit width	50 mm
Measurement travels to standard	1.5 mm / 4.8 mm / 15.0 mm / automatic / N x Lc freely selectable
Article no of the battery / rechargeable battery fitted	081575 LR6
Scanning speed	0.5 / 1.0 mm/s
Evaluation unit height	77 mm
maximum measuring range	350 µm
Number of batteries contained	1

Measurement travel for longitudinal sensing	1.25 / 4.0 / 12.5 mm
Cut-off ( $\lambda c$ )	0.25 / 0.8 / 2.5 mm
Weight of the evaluation unit	0.5 kg
Wireless application	HCT Mobile App
Series	HCT
Reversible reading	mm / inch
Interface	USB interface
Interface	Bluetooth interface
Calibration	Q2
Calibration	Q1
Type of product	Surface roughness measuring device

## Services

CalibrationRoughness standard Type R	029220 R
CalibrationSurface roughness measuring tool Type R	029200 R

## Accessories

Connection cable for feed unit	499036
Measuring stand ST-G for roughness measuring instruments with granite plate Type PST-G	498857 PST-G
Thermal paper for types ST1, ST2, H1, S2, M300, M310, M400 Type H1	499510 H1
Spare battery ST1, M300, M400	499549
Probe extension for ST2 / PS1 / PS10 / M300 and 310 Length 80 mm	499008 80
Probe for ST2 / PS1 / PS10 / M300 and 310 Type 6-350	499004 6-350
Probe guard for feed unit with projecting block Type	499038
Stand ST-D	499011
Stand mountingfor manual Vee ST2 / PS10 / M310	499035
Software Explorer	498847

Spare battery PS10, M310 including holder Type AKKU

499548 AKKU