



Base body Parallel shank, with through-coolant, 5×D, Type: 36



Order data

Order number	232250 36
GTIN	4045197589071
Item class	22G

Description

Version:

For holes up to IT10 accuracy.
With internal cooling.

Note:

Further sizes available on request.
Through-coolant: yes
Number of cutting edges Z: 2
Dia. range D_c : 36 - 47 mm
Reach L_1 : 209.6 mm
Shank $\varnothing D_s$: 40 mm
Shank length L_s : 70 mm
Clamping screws: 232990 TX20

Technical description

Reach L_1	209.6 mm
Shank $\varnothing D_s$	40 mm
Dia. range D_c	36 - 47 mm
Clamping screws	232990 TX20
Shank length L_s	70 mm
Number of cutting edges Z	2
Version	5×D
Shank	ISO 9766

Through-coolant	yes
Type of product	Indexable drill

Accessories

Torx® set of screws 10 pieces Drive TX15	232990 TX15
Torx® set of screws 10 pieces Drive TX20	232990 TX20
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600