

Garant
GARANT Master Mute boring bar, right-hand, Shank \varnothing / insert size: 25/11mm

Order data

Order number	260326 25/11
GTIN	4067263622918
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Overhang L_1	125 mm
Shank $\varnothing D_s$	25 mm
Pack of insert screws	269028 50
Insert size	11 mm
ISO code toolholder	A25X SDUCR/L11
Overall length L	222 mm
Setting angle κ	93 degrees
suitable indexable insert	DC.. 11T3..
Minimum pre-drill $\varnothing D_{min}$	32 mm
Centre offset L_3	17 mm
Series	Master Mute
non-clamping range S	155 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar