

Garant
GARANT Master Mute boring bar, right-hand, Shank \varnothing / insert size: 40/16mm

Order data

Order number	260920 40/16
GTIN	4067263623199
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

ISO code toolholder	A40X STFCCR/L16
Pack of insert screws	269028 50
Setting angle κ	90 degrees
Series	Master Mute
suitable indexable insert	TC.. 16T3..
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Insert size	16 mm
Shank $\varnothing D_s$	40 mm
Centre offset L_3	27 mm
Overall length L	345 mm
non-clamping range S	240 mm
Standard	DIN 8024
Application type	right-hand
Vibration	damped

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar