

Garant
GARANT Master Mute boring bar, left-hand, Shank \varnothing / insert size: 20/09mm

Order data

Order number	260045 20/09
GTIN	4067263623397
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Centre offset L_3	13 mm
Insert size	9 mm
Overall length L	177 mm
ISO code toolholder	A20X SCLCR/L09
Setting angle κ	95 degrees
Shank $\varnothing D_s$	20 mm
Series	Master Mute
Minimum pre-drill $\varnothing D_{min}$	25 mm
Pack of insert screws	269028 50
suitable indexable insert	CC.. 09T3..
Overhang L_1	100 mm
non-clamping range S	120 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar