

Garant
GARANT Master Tap Alu machine tap, DLC, MF: 14X1,5

Order data

Order number	136230 14X1,5
GTIN	4067263830610
Item class	11I

Description
Version:

High-performance tap, specially developed for **aluminium and non-ferrous alloys**. **Dynamic helical pitch** of the clamping slots ensure **optimum chip evacuation** and **process reliability**.

- **HSS-E-PM tool material – for high cutting edge stability.**
- **Ultra-smooth DLC coating for wear resistance and avoidance of edge build-up.**
- **Dynamic helical pitch of the flutes**
- **Short lead chamfer form E**

Technical description

Shank square <input type="checkbox"/>	9 mm
Thread Ø	14 mm
Tolerance class	ISO 2X 6HX
Thread size	M14×1.5
Tapping hole Ø	12.5 mm
Number of cutting edges Z	3
Shank Ø D _s	11 mm
Number of clamping slots	3
Overall length L	120 mm
Tool material	HSS E PM
Thread pitch	1.5 mm

Thread type	M
Standard	Works standard
Thread depth	42 mm
Coating	DLC
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	E
Helix angle	45 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Helix angle characteristic	unequal spacing
Colour ring	yellow
Series	Master Tap
Type of product	Taps

User data

	Suitability	V _c	ISO code
Aluminium	suitable	35 m/min	N
Aluminium (short chipping)	suitable	32 m/min	N
Alu > 10% Si	suitable	20 m/min	N
PMMA acrylic	suitable only under restricted conditions	20 m/min	N
PA 66	suitable only under restricted conditions	18 m/min	N
PEEK	suitable	18 m/min	N
Cu	suitable	18 m/min	N

CuZn	suitable	25 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		