

Garant
GARANT Master Mute boring bar, right-hand, Shank \varnothing / insert size: 16/07mm

Order data

Order number	260326 16/07
GTIN	4067263619796
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Centre offset L_3	11 mm
Setting angle κ	93 degrees
Overhang L_1	80 mm
ISO code toolholder	A16X SDUCR/L07
Shank $\varnothing D_s$	16 mm
Series	Master Mute
Insert size	7 mm
Pack of insert screws	269028 38
Minimum pre-drill $\varnothing D_{\min}$	20 mm
suitable indexable insert	DC.. 0702..
Overall length L	151 mm
non-clamping range S	96 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar