



LED floodlight with dimmer function CONNECT, Type: NOVA-10



Order data

Order number	081234 NOVA-10
GTIN	5708997006733
Item class	07A

Description

Version:

Scangrip CONNECT work lamps are based on the CAS system and are also compatible with 18-V batteries from all leading power tool manufacturers.

High-performance cordless LED floodlight with dimmer function. The housing is made of injection-moulded aluminium and is extremely robust and

resistant to strong blows, impacts and vibrations. For use with CAS 12 V and 18 V

Batteries, 18-V batteries from leading power tool manufacturers or direct connection to the SCANGRIP®

Power supply.

- **BLUETOOTH light control enables up to four lights to be switched on/off and the light output to be adjusted in five levels to suit the respective task.**
- **With removable diffuser.**
- **Integral carrying handle and new base for flexible alignment and for direct mounting on the SCANGRIP® stand or with magnetic holders.**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Lamps are supplied without battery and charger.

Note:

Suitable batteries, chargers and power supply units for wired power supply can be found under 073870 – 073890 and 081249.

Technical description

Number of rechargeable batteries contained	0
IP Index of Protection	IP 65
Power supply	Mains operated
Battery voltage	12 V
Battery voltage	18 V
Overall height	290 mm
Overall length	305 mm
Illumination	1000 - 10000 lm
Type of rechargeable battery	Lithium-ion
Overall width	125 mm
Type of product	Floodlight