



360° LED floodlight with dimmer function CONNECT, Type: AREA-10



Order data

Order number	081235 AREA-10
GTIN	5708997006757
Item class	07A

Description

Version:

Scangrip CONNECT work lamps are based on the CAS system and are also compatible with 18-V batteries from all leading power tool manufacturers.

High-performance cordless LED floodlight with uniform, non-dazzle illumination. The sturdy, shock-resistant plastic housing of the lamps is perfect for all working environments. Can be mounted on the SCANGRIP® stand. For CAS 18-V batteries, 18-V batteries from leading power tool manufacturers or direct connection to the SCANGRIP® power supply.

- **Beam dispersion angle of 360° or 180° can be selected.**
- **Dimmable in five lighting levels.**
- **BLUETOOTH light control enables up to four lights to be switched on/off and the light output to be adjusted in five levels to suit the respective task.**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Lamps are supplied without battery and charger.

Note:

Suitable batteries, chargers and power supply units for wired power supply can be found under 073870 – 073890 and 081249.

Technical description

Overall width	200 mm
IP Index of Protection	IP 65
Overall length	212 mm
Overall height	395 mm
Power supply	Mains operated
Battery voltage	12 V
Battery voltage	18 V
Illumination	1000 - 10000 lm
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Type of product	Area light