



12V rechargeable battery including charger, Type: M12NRG201



Order data

Order number	091241 M12NRG201
GTIN	4002395281497
Item class	03L

Description

Version:

Battery:

- **Intelligent control: REDLINK™ electronics.**
- **Overload protection – prevents accidental damage to the battery.**
- **Temperature management system – keeps the battery in the ideal temperature range to ensure maximum working life.**
- **Single-cell monitoring – ensures optimum charging and discharging for maximum working life.**
- **Deep discharge protection – prevents cell damage due to deep discharge.**
- **Up to 2× longer running time, 20% more power. In comparison to other Li-ion technologies and/or previous MILWAUKEE® battery technologies. Results depend on voltage, tool and application.**
- **Integrated, welded frame battery design with impact-sensitive separators, which prevent the battery from failing in the event of excessive vibration or falls.**
- **Can be used at extreme temperatures up to -20 °C, without impact on running time and service life.**
- **Discharge protection prevents cell damage due to overdischarge.**

Battery charger:

- **Electronic temperature control optimises the charging rate and thus protects against overheating and increases the battery life.**
- **The enclosed circuit board protects the electronics against dust, moisture and impacts.**
- **The LEDs light up step by step to indicate the current charge status of the rechargeable battery.**
- **REDLITHIUM™ 2.0 Ah batteries charge in 40 minutes or less.**

Supplied with:

1× M12 B2 battery pack and 1× C12 C charger.

Technical description

Charging time per battery	40 min
Battery capacity	2 Ah
Battery voltage	12 V
Weight per battery	200 g
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion